Litemask™ 4139G



UV/Visible Light/Heat/Activator Curable High Temperature Burnt-Off Mask

PRODUCT DESCRIPTION

Incure Litemask™ 4139G is an easy-to-use UV/Visible Light/LED/Heat Curing mask (gel) for temporary protection from chemical cleaning. Resistant to many chemicals, it does not affect the masked surfaces before and after cure. Product contains a 100% solids urethane acrylate and does not contain VOCs. The use of 4139G temporary masks help increase productivity and reduce labour content in plating and coating processes in electronics and aerospace industries. Mask can easily be burnt-off at 1200°F.

UNCURED PROPERTIES

Chemical Type Urethane Acrylate, 100% Solids, No Solvents					
Appearance	Single Component, Clear Transparent				
Density, g/ml	1.09	1.09 Refractive Index 1.51 @20°C			
Flash Point, °C	> 93 Toxicity Low (Refer to MSDS)				
Viscosity, cP	> 1,000,0	1,000,000 @0.5rpm			7
Other viscosities are a viscosity range reque this product may be p Email us at: support@ local distributor for mo	offering, b fee.	ASTM	D2556		

¹ Viscosity (cP) taken at 25°C - Call to enquiry for other viscosities

CURED PROPERTIES

JOHED I HOI EHHEO					
Shore Hardness, Durometer		D75 to D85	ASTM 2240		
Linear Shrinkage / Expansion (-ve)		2.20%	ASTM D2566		
Water Absorption at 24hrs		0.50%	² ISTM D570		
Tensile (PSI)	PC-PC / SS-SS	1,000* / 11,600*	ASTM 638		
* PC-PC / SS-SS / S-S / AL-AL * PC Substrate Failure	S-S / AL-AL	16,000* / 9,800*	ASTIVI 030		
Surface After Full Cure		Tack-Free	² ISTM D189		
Elongation at Break		55%	ASTM 638		
Thermal Range (Brittleness / Degrades) °C		-55 to 150	² ISTM D366		
Young's Modulus of Elasticity, MPa (PSI)		Not Available	3 ASTM 638		
Linear CTE (α1 & α2), ppm/°C		α1=32 , α2=92	² ISTM D696		


² ISTM - refers to Incure Standard Test Method

RECOMMENDED UV CURE SCHEDULE (FULL CURE)

1120011111212001 001120012 (1 022 00112)						
Full Cure Exposure Time			UVA	UVB	UVC	UVV
Fixture Time between glass slides m		mW/cm ²	223	56	4	215
Exposure Time (s)	1.0	mJ/cm ²	223	56	4	215
F200P™ @3.75" Dist	10.0	mW/cm ²	223	56	4	215
Belt Speed (ft/min)	5.5	mJ/cm ²	2,230	560	38	2,150
F500™ @3.0" Dist	5.0	mW/cm ²	436	127	12	390
Belt Speed (ft/min)	3.8	mJ/cm ²	2,180	635	58	1,950
S20™ Spot (4-Pole LG) 0.4" Dist		mW/cm ²	3,000	530	50	3,400
Exposure Time (s)	3.0	mJ/cm ²	9,000	1,590	150	10,200
L9000™ LED Spot @ 0.67" Dist mW		mW/cm ²	2,800	42	12	102
Exposure Time (s)	4.0	mJ/cm ²	11,200	168	48	408

Cure times on 8mm ø adhesive sample. Belt speeds using C9000-F200Px1AB (Flood) and C9000-F500x1AC (Focused Beam) conveyors for area curing. Please consult IncureLab™ for any other requi


TENSILE STRENGTH VS TEMPERATURE



UV INTENSITY REFERENCE TABLE

Incure UV Curing Lamp Model	⁴ Curing Distance vs UV Intensity					
Spot Curing (Diameter)	0.5" (12.6)	1" (25.4)	1.5" (38)	2" (50.8)	2.5" (63.5)	3" (76.2)
S20™ ARC (mW/cm²) / (ø mm)	1,400 (3)	1,500 (4)	650 (6)	360 (8)	240 (10)	175 (12)
L9000™ LED (mW/cm²) / (ø mm)	7,500 (9)	5,000 (10)	2,300 (17)	1,200 (20)	700 (25)	450 (30)
Flood/Focus Beam (Area)	UV Intensity (mW/cm²)					
F200™ ARC Flood (6" x 8")	325	280	245	215	190	165
F400™ ARC Flood (4" x 4")	860	570	440	345	270	215
F500™ ARC Focused (3" x 5")	1,040	685	530	415	325	260
L1044-365™ LED Flood (4" x 4")	2,675	2,380	1,900	1,625	1,430	1,280
L1044-405™ LED Flood (4" x 4")	2,950	2,625	2,150	1,900	1,650	1,450

⁴ Curing Distance is defined by the tip of light-guide or base of lamp housing to the bond area. All values are nominal with ±10% on, with LED Flood Static Uniformity at ±78% and Dynamic Uniformity at ±90%. Recommended curing parameters in grey



SECONDARY HEAT CURE SCHEDULE

Continuous Oven Bake	Duration
95°C (203°F)	120 mins
110°C (230°F)	60 mins
125°C (257°F)	30 mins

UV CURING SCHEDULE FOR THIS PRODUCT

Wavength λ	UVA (320 - 400nm)	UVB (290-320nm)	UVC (290-220nm)	VUV (400-700nm)
Minimum Intensity	223 mW/cm ²	56 mW/cm ²	4 mW/cm ²	215 mW/cm ²
Total Energy Required	2,230 mJ/cm ²	560 mJ/cm ²	38 mJ/cm ²	2,150 mJ/cm ²

Note: This product has been thoroughly tested to cure with F200P™ UV Flood Lamp. Intensity wavelengths (shaded) are crucial for curing this product. All measurements are made with EIT UV PowerPuck II. If you are unable to fully cure this product for some reasons, pls email us for assistance with your curing information.

SHELF-LIFE, STORAGE, USE AND HANDLING OF THIS PRODUCT

Shelf-Life of this unopened product is a minimum of SIX (6) months from date of manufacture. Avoid direct exposure of bottle to visible light at all times. Containers should remained covered when not in use. Product should be stored in a dark cool place of 10°C to 32°C. Transfer of product into other packages void all warranties. Users should ensure all bonding surfaces are free of grease, mold release, or any contaminants, as bonding performance will be compromised. All tests for cured bonds should be carried out at ambient temperature. For safe handling of this product, please read Material Safety Data-sheet (MSDS) prior to use. Organic solvents, such as IPA, may be used to wipe away uncured material from surfaces.

EtO and GAMMA STERILIZATION (Not Applicable for this Product)

All Incure medical products are formulated to subject to standard sterilization methods, such as EtO and Gamma Radiation of 25 to 50 kGrays (cumulative). Enhanced moisture and thermal resistance of this product show excellent adhesion and bonding strength after one cycle of steam auto-clave test. Depending on bond design and structure of the application, users should test specific assemblies after subjecting them to sterilisation. Consult Incure Support Team for assistance, if your devices are subjected to more than one sterilisation cycles.

NOTE

The data contained in this document are furnished for information only. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein. INCURE will not be liable for any indirect, special, incidental or consequential loss or damage arising from this INCURE product, regardless of the legal theory asserted. INCURE recommends that each user adequately test its proposed use and application before repetitive use, using this data as a guide.

Incure, Inc.

1 Hartford Square, Box 16 West,
Sulfa G-3, New Britain,
C7 06052, USA
1-16, (860) 744 2979

1-16, (860) 744 2979

1-16, (860) 746 2979

1-16, (860) 746 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16, (860) 747 2979

1-16



³ ASTM 638 Young's Modulus test speed @5mm/min for rigid and semi-rigid materials, @50mm/min for non-rigid materials, unless otherwise specified.